
FABORY



THERMAG Prevailing torqe type hexagon exhaust nut, all metal Steel Copper plated M8X13

Article number	72130.080.130
Brand	-
UBB	950355276391
UNSPSC	31161727
EAN	8715492912688
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M8
Driving features	Hexagon
Material	Steel
Thread direction	Right
Surface treatment	Copper plated
Thread	Metric thread
Info	Resistant to temperatures from -70 °C to +400 °C.

Standards

Technical Specification

d-D	M8
m (max.)	8.6
P	1.25
s	13

Technical Drawing

