FABORY



IMPULSE WRENCH 3/8 SHUT-OFF RRI-70RGT

Article number	RRI-70RGTRED
Brand	-
UBB	500619077182
UNSPSC	27112713
EAN	8717981203710
PKG. of 1	Full Box Only

Technical Parameters

Max. operation pressure	6.3
Tool insertion	3/8 inch
Angle model	Yes
Idle rotational speed	2000
Air inlet device-sided	R 1/4 inch
Max. loosening torque	45
Max. tightening torque	45
Attract torque adjustable	Yes
Impulse driver	Yes
Max. thread size (metric)	10
Air volume required	372

Standards