FABORY



Fabory Jobber drill Cylindrical DIN 338 HSSG Blanc 2,5 MM

Article number	U0001.025.001
Brand	-
UBB	240201380468
UNSPSC	23241639
EAN	8715494651486
PKG. of 10	Full Box Only

Technical Parameters

Total length	57
Diameter drill	2.5
Holding system	Cylindrical plug-in axle
Cutting length	30
Suitable for steel	Yes
Cutting material	Other
Tip angle	118
Shank shape	Cylindrical
Cutting direction	Right
Spiral drill	Yes

Standards

Technical Specification

Technical Drawing

