FABORY



Hexagon socket head cap screw UNC 1960 series ASME B18.3 Alloy steel ASTM A574 Plain 5/16-18X2.1/2

Article number	U07000.031.0250
Brand	-
UBB	500620904804
UNSPSC	31161605
EAN	8717077357891
PKG. of 25	Full Box Only

Technical Parameters

Diameter	5/16 Inch
Length	2.1/2 Inch
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Alloy steel
Material technical	ASTM A574
Thread direction	Right
Surface treatment	Plain
Thread	Unified National Coarse
Info	Marking in accordance with ASTM A574 with manufacturer's identification mark only.Attention: As the thread tolerance class for thread sizes up to and including 1 inch is 3A, plating can cause thread fit problems.Warning: electroplating of these products may cause hydrogen

Standards

ASME	B18.3

embrittlement.ft =
fully threaded

FABORY

Technical Specification

A	0.469
H	0.312
J	0.25
LT (min.)	1.12
Threads per inch	18

Technical Drawing

