FABORY



Hexagon socket countersunk head screw UNF ASME B18.3 Alloy steel ASTM F835 Plain #10-32X2 Inch

Article number	U07566.019.0200
Brand	-
UBB	500621046381
UNSPSC	31161518
EAN	8717077369146
PKG. of 100	Full Box Only

Technical Parameters

Diameter	NO.10
Length	2 Inch
Driving features	Hexagon socket
Head shape	Countersunk head
Material	Alloy steel
Material technical	ASTM F835
Thread direction	Right
Surface treatment	Plain
Thread	Unified National Fine
Info	ft = fully threadedAll dimensions in above table are in inches.Marking of these screws is not mandatory.Due to the unfavourable head geometry these fasteners have reduced loadability.Attention: As the thread tolerance class for thread sizes up to and including 1 inch is 3A, plating can

Standards

ASME	B18.3

cause thread fit problems.

FABORY

Technical Specification

A	0.411
H	0.127
J	0.125
LT (min.)	0.88
Threads per inch	32

Technical Drawing

