
FABORY



Carriage bolt UNC ASME B18.5 Steel SAE J429 Zinc plated Gr.5 1/4-20X3 Inch

Article number	U08320.025.0300
Brand	-
UBB	500624001433
UNSPSC	31161612
EAN	8717077380691
PKG. of 50	Full Box Only

Technical Parameters

Diameter	1/4 Inch
Length	3 Inch
Class	Gr.5
Material	Steel
Material technical	SAE J429
Thread direction	Right
Surface treatment	Zinc plated
Thread	Unified National Coarse

Standards

ASME	B18.5

Technical Specification

O (max.)	0.26
P (max.)	0.156
A (max.)	0.594
H (max.)	0.145
LT (min.): L6 Inch	1
LT (min.): L≤6 Inch	0.75
Threads per inch	20

Technical Drawing

