
FABORY



Machine screw pan head UNC asme B18.6.3 ASME B18.6.3 Low carbon steel Zinc plated #10-24X5/8

Article number	U24522.019.0062
Brand	-
UBB	500624939731
UNSPSC	31161504
EAN	8717077793118
PKG. of 100	Full Box Only

Technical Parameters

Diameter	NO.10
Length	5/8 Inch
Driving features	Phillips
Head shape	Pan head
Material	Low carbon steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Unified National Coarse
Threads per inch	24
Info	Screws with diameter ≤ No.5 and length ≤ 1.1/8 inch are fully threaded, longer screws are threaded 1 inch min.Screws with diameter No.5 and length ≤ 2 inch are fully threaded, longer screws are threaded 1.1/2 inch min.

Standards

ASME	B18.6.3

Technical Specification

A (max.)	0.373
H (max.)	0.133

Technical Drawing

No. cross recess 2

FABORY

