FABORY



Machine screw truss UNC asme B18.6.3 ASME B18.6.3 Stainless steel A2 (AISI 304/18-8) #6-32X5/16

Article number	U51862.013.0031
Brand	-
UBB	500625056519
UNSPSC	31161504
EAN	8712423001169
PKG. of 100	Full Box Only

Technical Parameters

Diameter	NO.6
Length	5/16 Inch
Driving features	Phillips
Head shape	Truss head
Material	Stainless steel
Material technical	ASTM F837 304
Thread direction	Right
Thread	Unified National Coarse
Threads per inch	32
Info	Screws with diameter ≤ No.5 and length ≤ 1.1/8 inch are fully threaded, longer screws are threaded 1 inch min.Screws with diameter No.5 and length ≤ 2 inch are fully threaded, longer screws are threaded 1.1/2 inch min.

Standards

ASME	B18.6.3

Technical Specification

A (max.)	0.321
H (max.)	0.086

Technical Drawing

No. cross recess 2

FABORY

