FABORY

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Plain, Class 8.8 M18X150

Article number	01000.180.150
Brand	-
UBB	950351014507
UNSPSC	31161620
EAN	8715492008985
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M18
Length	150 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

ASME	B18.2.3.1M
NF	E25-112
DIN	931
ISO	4014
NEN	1555

Technical Specification

b (min.): 125mmL≤200mm	48
b (min.): L200mm	61
b (min.): L≤125mm	42
d-D	M18
k	11.5
L (mm)	150
P	2.5
s	27

Technical Drawing

