FABORY

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Plain, Class 8.8 M24X100

Article number	01000.240.100
Brand	-
UBB	950351019977
UNSPSC	31161620
EAN	8715492009838
PKG. of 10	Full Box Only

Technical Parameters

Diameter	M24
Length	100 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

DIN	931
NF	E25-112
ISO	4014
ASME	B18.2.3.1M
NEN	1555

Technical Specification

b (min.): 125mmL≤200mm	60
b (min.): L200mm	73
b (min.): L≤125mm	54
d-D	M24
k	15
L (mm)	100
P	3
s	36

Technical Drawing

