FABORY

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Plain, Class 8.8 M24X250

Article number	01000.240.250
Brand	-
UBB	950351915273
UNSPSC	31161620
EAN	8715492009999
PKG. of 10	Full Box Only

Technical Parameters

Diameter	M24
Length	250 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

NEN	1555
NF	E25-112
DIN	931
ISO	4014
ASME	B18.2.3.1M

Technical Specification

b (min.): 125mmL≤200mm	60
b (min.): L200mm	73
b (min.): L≤125mm	54
d-D	M24
k	15
L (mm)	250
P	3
s	36

Technical Drawing

