FABORY

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Plain, Class 8.8 M30X480

Article number	01000.300.480
Brand	-
UBB	950351026642
UNSPSC	31161620
EAN	8715492010759
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M30
Length	480 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

DIN	931
ISO	4014
NF	E25-112
ASME	B18.2.3.1M
NEN	1555

Technical Specification

b (min.): 125mmL≤200mm	72
b (min.): L200mm	85
b (min.): L≤125mm	66
d-D	M30
k	18.7
L (mm)	480
P	3.5
s	46

Technical Drawing

