FABORY

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Plain, Class 8.8 M33X240

Article number	01000.330.240
Brand	-
UBB	950351027970
UNSPSC	31161620
EAN	8715492010902
PKG. of 2	Full Box Only

Technical Parameters

Diameter	M33
Length	240 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

NEN	1555
DIN	931
NF	E25-112
ISO	4014
ASME	B18.2.3.1M

Technical Specification

b (min.): 125mmL≤200mm	78
b (min.): L200mm	91
b (min.): L≤125mm	72
d-D	M33
k	21
L (mm)	240
P	3.5
s	50

Technical Drawing

