FABORY

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Plain, Class 8.8 M52X180

Article number	01000.520.180
Brand	-
UBB	950351036054
UNSPSC	31161620
EAN	8715492012326
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M52
Length	180 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

DIN	931
ISO	4014
NF	E25-112
ASME	B18.2.3.1M
NEN	1555

Technical Specification

b (min.): 125mmL≤200mm	116
b (min.): L200mm	119
d-D	M52
k	33
L (mm)	180
P	5
s	80

Technical Drawing

