FABORY



DIN 931 Partially Threaded Metric Hexagon Head Bolt, Zinc Plated, Class 8.8 M5X30

Article number	01200.050.030
Brand	-
UBB	950351140658
UNSPSC	31161620
EAN	8715492024756
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M5
Length	30 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

NF	E25-112
NEN	1555
DIN	931
ASME	B18.2.3.1M
ISO	4014

Technical Specification

b (min.): 125mmL≤200mm	22
b (min.): L≤125mm	16
d-D	M5
k	3.5
L (mm)	30
P	0.8
s	8

Technical Drawing

