FABORY



# DIN 931 Partially Threaded Metric Hexagon Head Bolt, Zinc Plated, Class 8.8 M5X80

| | |
|---|---|
| Article number | 01200.050.080 |
| Brand | - |
| UBB | 950351141490 |
| UNSPSC | 31161620 |
| EAN | 8715492024855 |
| PKG. of 200 | Full Box Only |

## Technical Parameters

| | |
|---|---|
| Diameter | M5 |
| Length | 80 mm |
| Class | 8.8 |
| Driving features | Hexagon |
| Head shape | Hexagon head |
| Material | Steel |
| Thread direction | Right |
| Surface treatment | Zinc plated |
| Thread | Metric thread |

## Standards

| | |
|---|---|
| DIN | 931 |
| NF | E25-112 |
| NEN | 1555 |
| ISO | 4014 |
| ASME | B18.2.3.1M |

## Technical Specification

| | |
|---|---|
| b (min.): 125mmL≤200mm | 22 |
| b (min.): L≤125mm | 16 |
| d-D | M5 |
| k | 3.5 |
| L (mm) | 80 |
| P | 0.8 |
| s | 8 |

## Technical Drawing

