FABORY



DIN 931 Partially Threaded Metric Hexagon Head Bolt, Zinc Plated, Class 8.8 M8X180

Article number	01200.080.180
Brand	-
UBB	950351145608
UNSPSC	31161620
EAN	8715492025418
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M8
Length	180 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

NF	E25-112
ISO	4014
DIN	931
ASME	B18.2.3.1M
NEN	1555

Technical Specification

b (min.): 125mmL≤200mm	28
b (min.): L≤125mm	22
d-D	M8
k	5.3
L (mm)	180
P	1.25
s	13

Technical Drawing

