FABORY



DIN 931 Partially Threaded Metric Hexagon Head Bolt, Zinc Plated, Class 8.8 M10X130/S=17

Article number	01200.100.130
Brand	-
UBB	950351147273
UNSPSC	31161620
EAN	8715492025722
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M10
Length	130 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

DIN	931
ASME	B18.2.3.1M
NEN	1555
NF	E25-112
ISO	4014

Technical Specification

b (min.): 125mmL≤200mm	32
b (min.): L200mm	45
b (min.): L≤125mm	26
d-D	M10
k	6.4
L (mm)	130
P	1.5
s	17

Technical Drawing

