FABORY



DIN 931 Partially Threaded Metric Hexagon Head Bolt, Zinc Plated, Class 8.8 M12X55/S=19

Article number	01200.120.055
Brand	-
UBB	950351148180
UNSPSC	31161620
EAN	8715492025876
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M12
Length	55 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ISO	4014
NF	E25-112
DIN	931
ASME	B18.2.3.1M
NEN	1555

Technical Specification

b (min.): 125mmL≤200mm	36
b (min.): L200mm	49
b (min.): L≤125mm	30
d-D	M12
k	7.5
L (mm)	55
P	1.75
s	19

Technical Drawing

