FABORY



# DIN 933 Fully Threaded Metric Hexagon Head Bolt, Zinc Plated, Class 8.8 M27X140

| | |
|---|---|
| Article number | 01210.270.140 |
| Brand | - |
| UBB | 950351083643 |
| UNSPSC | 31161620 |
| EAN | 8715492032201 |
| PKG. of 10 | Full Box Only |

## Technical Parameters

| | |
|---|---|
| Diameter | M27 |
| Length | 140 mm |
| Class | 8.8 |
| Driving features | Hexagon |
| Head shape | Hexagon head |
| Material | Steel |
| Thread direction | Right |
| Surface treatment | Zinc plated |
| Thread | Metric thread |

## Standards

| | |
|---|---|
| ASME | B18.2.3.1M |
| NF | E25-114 |
| NEN | 1568 |
| ISO | 4017 |
| DIN | 933 |

## Technical Specification

| | |
|---|---|
| d-D | M27 |
| k | 17 |
| L (mm) | 140 |
| P | 3 |
| s | 41 |

## Technical Drawing

