FABORY

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Zinc Plated Yellow Passivated, Class 8.8 M6X90

Article number	01220.060.090
Brand	-
UBB	952351192119
UNSPSC	31161620
EAN	8715492033178
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M6
Length	90 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread

Standards

DIN	931
ISO	4014
NEN	1555
ASME	B18.2.3.1M
NF	E25-112

Technical Specification

b (min.): 125mmL≤200mm	24
b (min.): L≤125mm	18
d-D	M6
k	4
L (mm)	90
P	1
s	10

Technical Drawing

