FABORY

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Zinc Plated Yellow Passivated, Class 8.8 M8X100

Article number	01220.080.100
Brand	-
UBB	950351168055
UNSPSC	31161620
EAN	8715492033352
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M8
Length	100 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread

Standards

ASME	B18.2.3.1M
NF	E25-112
NEN	1555
DIN	931
ISO	4014

Technical Specification

b (min.): 125mmL≤200mm	28
b (min.): L≤125mm	22
d-D	M8
k	5.3
L (mm)	100
P	1.25
s	13

Technical Drawing

