FABORY

# DIN 931 Partially Threaded Metric Hexagon Head Bolt, Zinc Plated Yellow Passivated, Class 8.8 M8X110

| | |
|---|---|
| Article number | 01220.080.110 |
| Brand | - |
| UBB | 952351328341 |
| UNSPSC | 31161620 |
| EAN | 8715492033369 |
| PKG. of 100 | Full Box Only |

## Technical Parameters

| | |
|---|---|
| Diameter | M8 |
| Length | 110 mm |
| Class | 8.8 |
| Driving features | Hexagon |
| Head shape | Hexagon head |
| Material | Steel |
| Thread direction | Right |
| Surface treatment | Zinc plated yellow passivated |
| Thread | Metric thread |

## Standards

| | |
|---|---|
| ISO | 4014 |
| ASME | B18.2.3.1M |
| DIN | 931 |
| NF | E25-112 |
| NEN | 1555 |

## Technical Specification

| | |
|---|---|
| b (min.): 125mmL≤200mm | 28 |
| b (min.): L≤125mm | 22 |
| d-D | M8 |
| k | 5.3 |
| L (mm) | 110 |
| P | 1.25 |
| s | 13 |

## Technical Drawing

