FABORY

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Zinc Plated Yellow Passivated, Class 8.8 M14X80/S=22

Article number	01220.140.080
Brand	-
UBB	950351170358
UNSPSC	31161620
EAN	8715492034038
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M14
Length	80 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread

Standards

NEN	1555
DIN	931
ISO	4014
ASME	B18.2.3.1M
NF	E25-112

Technical Specification

b (min.): 125mmL≤200mm	40
b (min.): L200mm	53
b (min.): L≤125mm	34
d-D	M14
k	8.8
L (mm)	80
P	2
s	22

Technical Drawing

