FABORY

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Zinc Plated Yellow Passivated, Class 8.8 M14X200/S=22

Article number	01220.140.200
Brand	-
UBB	954351335250
UNSPSC	31161620
EAN	8715492034137
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M14
Length	200 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread

Standards

NEN	1555
ISO	4014
NF	E25-112
DIN	931
ASME	B18.2.3.1M

Technical Specification

b (min.): 125mmL≤200mm	40
b (min.): L200mm	53
b (min.): L≤125mm	34
d-D	M14
k	8.8
L (mm)	200
P	2
s	22

Technical Drawing

