FABORY

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Zinc Plated Yellow Passivated, Class 8.8 M16X55

Article number	01220.160.055
Brand	-
UBB	952351308871
UNSPSC	31161620
EAN	8715492034151
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M16
Length	55 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread

Standards

ISO	4014
NEN	1555
DIN	931
ASME	B18.2.3.1M
NF	E25-112

Technical Specification

b (min.): 125mmL≤200mm	44
b (min.): L200mm	57
b (min.): L≤125mm	38
d-D	M16
k	10
L (mm)	55
P	2
s	24

Technical Drawing

