FABORY

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Zinc Plated Yellow Passivated, Class 8.8 M16X120

Article number	01220.160.120
Brand	-
UBB	950351171349
UNSPSC	31161620
EAN	8715492034250
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M16
Length	120 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread

Standards

NF	E25-112
NEN	1555
DIN	931
ASME	B18.2.3.1M
ISO	4014

Technical Specification

b (min.): 125mmL≤200mm	44
b (min.): L200mm	57
b (min.): L≤125mm	38
d-D	M16
k	10
L (mm)	120
P	2
s	24

Technical Drawing

