FABORY

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Zinc Plated Yellow Passivated, Class 8.8 M20X80

Article number	01220.200.080
Brand	-
UBB	950351171752
UNSPSC	31161620
EAN	8715492034557
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M20
Length	80 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread

Standards

ASME	B18.2.3.1M
NF	E25-112
ISO	4014
NEN	1555
DIN	931

Technical Specification

b (min.): 125mmL≤200mm	52
b (min.): L200mm	65
b (min.): L≤125mm	46
d-D	M20
k	12.5
L (mm)	80
P	2.5
s	30

Technical Drawing

