FABORY

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Zinc Plated Yellow Passivated, Class 8.8 M24X100

Article number	01220.240.100
Brand	-
UBB	950351172586
UNSPSC	31161620
EAN	8715492034946
PKG. of 10	Full Box Only

Technical Parameters

Diameter	M24
Length	100 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread

Standards

ISO	4014
NEN	1555
NF	E25-112
ASME	B18.2.3.1M
DIN	931

Technical Specification

b (min.): 125mmL≤200mm	60
b (min.): L200mm	73
b (min.): L≤125mm	54
d-D	M24
k	15
L (mm)	100
P	3
s	36

Technical Drawing

