FABORY

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Zinc Plated Yellow Passivated, Class 8.8 M27X120

Article number	01220.270.120
Brand	-
UBB	954351293749
UNSPSC	31161620
EAN	8715492035134
PKG. of 10	Full Box Only

Technical Parameters

Diameter	M27
Length	120 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread

Standards

DIN	931
NEN	1555
ISO	4014
ASME	B18.2.3.1M
NF	E25-112

Technical Specification

b (min.): 125mmL≤200mm	66
b (min.): L200mm	79
b (min.): L≤125mm	60
d-D	M27
k	17
L (mm)	120
P	3
s	41

Technical Drawing

