FABORY

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Zinc Flake Cr6+ Free, Class 8.8 M6X35

Article number	01226.060.035
Brand	-
UBB	500571899581
UNSPSC	31161620
EAN	8715494282390
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M6
Length	35 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc flake Cr6+free - ISO 10683 flZnnc
Thread	Metric thread
Info	A zinc flake coating eliminates the risk of hydrogen embrittlement.

Standards

ASME	B18.2.3.1M
ISO	4014
DIN	931
NF	E25-112
NEN	1555

Technical Specification

b (min.): 125mmL≤200mm	24
b (min.): L≤125mm	18
d-D	M6
k	4
L (mm)	35
P	1
s	10

Technical Drawing

