FABORY

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Zinc Flake Cr6+ Free, Class 8.8 M6X50

Article number	01226.060.050
Brand	-
UBB	500571899821
UNSPSC	31161620
EAN	8715494282420
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M6
Length	50 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc flake Cr6+free - ISO 10683 flZnnc
Thread	Metric thread
Info	A zinc flake coating eliminates the risk of hydrogen embrittlement.

Standards

DIN	931
ISO	4014
NEN	1555
ASME	B18.2.3.1M
NF	E25-112

Technical Specification

b (min.): 125mmL≤200mm	24
b (min.): L≤125mm	18
d-D	M6
k	4
L (mm)	50
P	1
s	10

Technical Drawing

