FABORY

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Zinc Flake Cr6+ Free, Class 8.8 M8X35

Article number	01226.080.035
Brand	-
UBB	500571900066
UNSPSC	31161620
EAN	8715494282444
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M8
Length	35 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc flake Cr6+free - ISO 10683 flZnnc
Thread	Metric thread
Info	A zinc flake coating eliminates the risk of hydrogen embrittlement.

Standards

NEN	1555
DIN	931
NF	E25-112
ASME	B18.2.3.1M
ISO	4014

Technical Specification

b (min.): 125mmL≤200mm	28
b (min.): L≤125mm	22
d-D	M8
k	5.3
L (mm)	35
P	1.25
s	13

Technical Drawing

