FABORY

Hexagon nut ISO 4032 Steel Zinc plated yellow passivated 8 M12

Article number	01321.120.001
Brand	-
UBB	950355965506
UNSPSC	31161727
EAN	8715492406880
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M12
Class	8
Driving features	Hexagon
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread

Standards

ISO	4032

Technical Specification

d-D	M12
m (max.)	10.8
P	1.75
s	18

Technical Drawing

