FABORY

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Hot Dip Galvanised, Class 8.8 M30X200

Article number	01400.300.200
Brand	-
UBB	950351199084
UNSPSC	31161620
EAN	8715492409751
PKG. of 10	Full Box Only

Technical Parameters

Diameter	M30
Length	200 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Hot dip galvanized
Thread	Metric thread
Info	ISO metric hot dip galvanized bolts and screws are manufactured with thread tolerance class 6az (undersize) before coating.After galvanizing they will fit into standard nuts and threaded holes with thread tolerance class 6H.ISO metric

Standards

NF	E25-112
ISO	4014
DIN	931
ASME	B18.2.3.1M
NEN	1555

Technical Specification

b (min.): 125mmL≤200mm	72
b (min.): L200mm	85

Technical Drawing

b (min.): L≤125mm	66
d-D	M30
k	18.7
L (mm)	200
P	3.5
s	46

