FABORY

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Zinc Plated, Class 10.9 M24X80

Article number	04102.240.080
Brand	-
UBB	500648138898
UNSPSC	31161620
EAN	8717077209756
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M24
Length	80 mm
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread
Info	Warning: electroplating of these products may cause hydrogen embrittlement.

Standards

DIN	931
ISO	4014
ASME	B18.2.3.1M
NF	E25-112
NEN	1555

Technical Specification

b (min.): 125mmL≤200mm	60
b (min.): L200mm	73
b (min.): L≤125mm	54
d-D	M24
k	15
L (mm)	80
P	3

Technical Drawing

