FABORY

# DIN 931 Partially Threaded Metric Hexagon Head Bolt, Zinc Flake Cr6+ Free, Class 10.9 M10X100

| | |
|---|---|
| Article number | 04105.100.100 |
| Brand | - |
| UBB | 500505561380 |
| UNSPSC | 31161620 |
| EAN | 8715494439190 |
| PKG. of 100 | Full Box Only |

## Technical Parameters

| | |
|---|---|
| Diameter | M10 |
| Length | 100 mm |
| Class | 10.9 |
| Driving features | Hexagon |
| Head shape | Hexagon head |
| Material | Steel |
| Thread direction | Right |
| Surface treatment | Zinc flake Cr6+free - ISO 10683 flZnnc |
| Thread | Metric thread |
| Info | A zinc flake coating eliminates the risk of hydrogen embrittlement. |

## Standards

| | |
|---|---|
| NF | E25-112 |
| ASME | B18.2.3.1M |
| DIN | 931 |
| ISO | 4014 |
| NEN | 1555 |

## Technical Specification

| | |
|---|---|
| b (min.): 125mmL≤200mm | 32 |
| b (min.): L200mm | 45 |
| b (min.): L≤125mm | 26 |
| d-D | M10 |
| k | 6.4 |
| L (mm) | 100 |
| P | 1.5 |

## Technical Drawing

