FABORY

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Zinc Flake Cr6+ Free, Class 10.9 M10X120

Article number	04105.100.120
Brand	-
UBB	500574308168
UNSPSC	31161620
EAN	8715494301626
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M10
Length	120 mm
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc flake Cr6+free - ISO 10683 flZnnc
Thread	Metric thread
Info	A zinc flake coating eliminates the risk of hydrogen embrittlement.

Standards

ISO	4014
ASME	B18.2.3.1M
NF	E25-112
DIN	931
NEN	1555

Technical Specification

b (min.): 125mmL≤200mm	32
b (min.): L200mm	45
b (min.): L≤125mm	26
d-D	M10
k	6.4
L (mm)	120
P	1.5

Technical Drawing

