FABORY

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Zinc Flake Cr6+ Free, Class 10.9 M12X80

Article number	04105.120.080
Brand	-
UBB	500505561950
UNSPSC	31161620
EAN	8715494439312
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M12
Length	80 mm
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc flake Cr6+free - ISO 10683 flZnnc
Thread	Metric thread
Info	A zinc flake coating eliminates the risk of hydrogen embrittlement.

Standards

DIN	931
NF	E25-112
ASME	B18.2.3.1M
NEN	1555
ISO	4014

Technical Specification

b (min.): 125mmL≤200mm	36
b (min.): L200mm	49
b (min.): L≤125mm	30
d-D	M12
k	7.5
L (mm)	80
P	1.75

Technical Drawing

