FABORY

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Zinc Flake Cr6+ Free, Class 10.9 M16X90

Article number	04105.160.090
Brand	-
UBB	500505563287
UNSPSC	31161620
EAN	8715494439534
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M16
Length	90 mm
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc flake Cr6+free - ISO 10683 flZnnc
Thread	Metric thread
Info	A zinc flake coating eliminates the risk of hydrogen embrittlement.

Standards

ASME	B18.2.3.1M
ISO	4014
DIN	931
NF	E25-112
NEN	1555

Technical Specification

b (min.): 125mmL≤200mm	44
b (min.): L200mm	57
b (min.): L≤125mm	38
d-D	M16
k	10
L (mm)	90
P	2

Technical Drawing

