FABORY



Hexagon socket head cap screw DIN 912 Steel Plain 10.9 M33X140

Article number	07015.330.140
Brand	-
UBB	500644768854
UNSPSC	31161605
EAN	8717077025431
PKG. of 5	Full Box Only

Technical Parameters

Diameter	M33
Length	140 mm
Class	10.9
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread
Info	Warning: electroplating of these products may cause hydrogen embrittlement.

Standards

NEN	1241
ISO	4762
BS	4168-1
ASME	B18.3.1M
DIN	912
NF	E25-125

Technical Specification

b	78
d-D	M33
dk (max.)	50
Full thread if L ≤	100
k (max.)	33
L (mm)	140
P	3.5
s	24

Technical Drawing

