FABORY



Hexagon socket head cap screw DIN 912 Steel Zinc flake Cr6+free - ISO 10683 flZnnc 10.9 M12X50

Article number	07021.120.050
Brand	-
UBB	500647929271
UNSPSC	31161605
EAN	8717077280946
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M12
Length	50 mm
Class	10.9
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Zinc flake Cr6+free - ISO 10683 flZnnc
Thread	Metric thread
Info	A zinc flake coating eliminates the risk of hydrogen embrittlement.

Standards

NEN	1241
DIN	912
ISO	4762
ASME	B18.3.1M
BS	4168-1
NF	E25-125

Technical Specification

b	36
d-D	M12
dk (max.)	18
Full thread if L ≤	50
k (max.)	12
L (mm)	50
P	1.75
s	10

Technical Drawing

