FABORY



Hexagon socket head cap screw DIN 912 Steel Zinc plated 10.9 M36X90

Article number	07023.360.090
Brand	-
UBB	500647967040
UNSPSC	31161605
EAN	8717077284722
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M36
Length	90 mm
Class	10.9
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread
Info	Warning: electroplating of these products may cause hydrogen embrittlement.

Standards

ASME	B18.3.1M
NEN	1241
NF	E25-125
BS	4168-1
DIN	912
ISO	4762

Technical Specification

b	84
d-D	M36
dk (max.)	54
Full thread if L ≤	110
k (max.)	36
L (mm)	90
P	4
s	27

Technical Drawing

