FABORY



Hexagon socket head cap screw DIN 912 Steel Zinc flake Cr6+free - ISO 10683 flZnnc 8.8 M3X10

Article number	07065.030.010
Brand	-
UBB	500577358913
UNSPSC	31161605
EAN	8715494328746
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M3
Length	10 mm
Class	8.8
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Zinc flake Cr6+free - ISO 10683 flZnnc
Thread	Metric thread
Info	A zinc flake coating eliminates the risk of hydrogen embrittlement.

Standards

ASME	B18.3.1M
NEN	1241
DIN	912
NF	E25-125
ISO	4762
BS	4168-1

Technical Specification

b	18
d-D	M3
dk (max.)	5.5
Full thread if L ≤	20
k (max.)	3
L (mm)	10
P	0.5
s	2.5

Technical Drawing

