FABORY



Hexagon socket head cap screw DIN 912 Steel Zinc flake Cr6+free - ISO 10683 flZnnc 8.8 M5X12

Article number	07065.050.012
Brand	-
UBB	500577360307
UNSPSC	31161605
EAN	8715494328883
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M5
Length	12 mm
Class	8.8
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Zinc flake Cr6+free - ISO 10683 flZnnc
Thread	Metric thread
Info	A zinc flake coating eliminates the risk of hydrogen embrittlement.

Standards

BS	4168-1
ISO	4762
DIN	912
NF	E25-125
NEN	1241
ASME	B18.3.1M

Technical Specification

b	22
d-D	M5
dk (max.)	8.5
Full thread if L ≤	25
k (max.)	5
L (mm)	12
P	0.8
s	4

Technical Drawing

