FABORY



Hexagon socket head cap screw with low head DIN 7984 Steel Zinc plated 08.8 M10X12

Article number	07090.100.012
Brand	-
UBB	500645089011
UNSPSC	31161605
EAN	8717077058781
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M10
Length	12 mm
Class	08.8
Driving features	Hexagon socket
Head shape	Low cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread
Info	Due to the unfavourable head geometry these fasteners have reduced loadability.Steel fasteners with reduced loadability are marked with a '0' preceding the property class mark, e.g. '010.9'.Stainless steel fasteners with reduced loadability are either marked with a '0' preceding the property class mark, e.g. 'A2-070',

Standards

DIN	7984

or with the steel grade only, e.g. 'A2'.

FABORY

Technical Specification

b (min.)	26
d-D	M10
dk	16
Full thread if L ≤	35
k	6
L (mm)	12
P	1.5
s	7

Technical Drawing

