FABORY



Hexagon socket button head screw with flange ISO 7380-2 Steel Zinc plated 010.9 M3X12

Article number	07141.030.012
Brand	-
UBB	951351887538
UNSPSC	31161518
EAN	8715492067531
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M3
Length	12 mm
Class	010.9
Driving features	Hexagon socket
Head shape	Button head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread
Info	Warning: electroplating of these products may cause hydrogen embrittlement.Due to the unfavourable head geometry these fasteners have reduced loadability.Steel fasteners with reduced loadability are marked with a '0' preceding the property class mark, e.g. '010.9'.Stainless steel fasteners with reduced loadability are either marked

Standards

ISO	7380-2

with a '0' preceding the property class mark, e.g. 'A2-070', or with the steel grade only, e.g. 'A2'.

Technical Specification

d-D	M3
dc (max.)	6.9
Full thread if L ≤	20
k (max.)	1.65
L (mm)	12
P	0.5
s	2

Technical Drawing

