FABORY



Hexagon socket head cap screw DIN 912 Steel Zinc plated 8.8 M27X90

Article number	07160.270.090
Brand	-
UBB	500644827684
UNSPSC	31161605
EAN	8717077031319
PKG. of 10	Full Box Only

Technical Parameters

Diameter	M27
Length	90 mm
Class	8.8
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ASME	B18.3.1M
DIN	912
NF	E25-125
ISO	4762
BS	4168-1
NEN	1241

Technical Specification

b	66
d-D	M27
dk (max.)	40
Full thread if L ≤	90
k (max.)	27
L (mm)	90
P	3
s	19

Technical Drawing

