FABORY



Hexagon socket countersunk head screw ISO 10642 Steel Plain 010.9 M18X90

Article number	07400.180.090
Brand	-
UBB	952351364395
UNSPSC	31161518
EAN	8715492084217
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M18
Length	90 mm
Class	010.9
Driving features	Hexagon socket
Head shape	Countersunk head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread
Info	Warning: electroplating of these products may cause hydrogen embrittlement.All thread lengths are guide values only and may deviate.Due to the unfavourable head geometry these fasteners have reduced loadability.Steel fasteners with reduced loadability are marked with a '0' preceding the property class mark,

Standards

DIN	≈7991
ISO	10642

e.g. '010.9'.Stainless steel fasteners with reduced loadability are either marked with a '0' preceding the property class mark, e.g. 'A2-070', or with the steel grade only, e.g. 'A2'.

Technical Specification

b (min.)	42
d-D	M18
dk (max.)	33
Full thread if L ≤	60
k (max.)	8
L (mm)	90
P	2.5
s	12
α	90

Technical Drawing

