FABORY



Hexagon socket countersunk head screw ISO 10642 Steel Zinc plated 8.8 M3X20

Article number	07470.030.020
Brand	-
UBB	950351486184
UNSPSC	31161518
EAN	8715492151049
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M3
Length	20 mm
Class	08.8
Driving features	Hexagon socket
Head shape	Countersunk head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread
Info	All thread lengths are guide values only and may deviate.Due to the unfavourable head geometry these fasteners have reduced loadability.Steel fasteners with reduced loadability are marked with a '0' preceding the property class mark, e.g. '010.9'.Stainless steel fasteners with reduced loadability are either marked with a '0' preceding

Standards

ISO	10642
DIN	≈7991

the property class mark, e.g. 'A2-070', or with the steel grade only, e.g. 'A2'.

Technical Specification

b (min.)	18
d-D	M3
dk (max.)	5.81
Full thread if L ≤	25
k (max.)	1.86
L (mm)	20
P	0.5
s	2
α	90

Technical Drawing

